

Product data sheet

Characteristics

56SPO315-RW

56 Series Pendant Outlet - Switched - 3 Pin - 15A - 250V



Main

Range of product	Series 56
Range	Clipsal - 56 Series
Product brand	Clipsal
Product or component type	Pendant outlet
Device application	Power supply
Colour	White (RAL 9003)

Complementary

Number of poles	2
Plug, socket category	Low voltage
Plug, socket, control station shape	Straight
[In] rated current	15 A
[Ue] rated operational voltage	250 V AC 50 Hz conforming to EN 60309-2
Poles description	1P + N + E
Voltage colour	Blue
Duration	6 h
Material	PBT (polybutylene terephthalate): housing
Contacts material	Sleeves: brass
Connections - terminals	Screw terminals 0.75...2.5 mm ²
Connections - terminals	Screw terminal
Socket number	1
Outlet standard	Industrial
Cable outer diameter	7...10 mm
Cable entry	Cable gland
Thread type	M20
Net weight	0.26 kg
Depth	183 mm
Width	83 mm
Height	83 mm
Targeted country	Australia

Environment

IP degree of protection	IP66 conforming to AS 60529
Ambient air temperature for operation	-25...75 °C
Standards	AS/NZS 3120

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	210 g
Package 1 Height	78 mm
Package 1 width	94 mm
Package 1 Length	176 mm

Offer Sustainability

Sustainable offer status	Green Premium product
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile