

## Product data sheet

### Characteristics

# 56SW110/2LE-RO

Clipsal - 56 Series, Surface Switch PVC 1  
Gang 2 Way 10A Less Enclosure



### Main

|                           |                                     |
|---------------------------|-------------------------------------|
| Range of product          | Series 56                           |
| Range                     | Clipsal - 56 Series                 |
| Product brand             | Clipsal                             |
| Product or component type | Switch                              |
| Device presentation       | Basic element with full cover plate |
| Device application        | Control                             |
| Colour                    | Cover: orange                       |
| Handle colour             | Grey                                |
| Suitability for isolation | No                                  |

### Complementary

|                                |                    |
|--------------------------------|--------------------|
| Switch function                | 1-pole             |
| Poles description              | 1P                 |
| Control type                   | Rotary knob        |
| Number of poles                | 1                  |
| Device mounting                | Surface            |
| Material                       | PC (polycarbonate) |
| Tightening torque              | 0.8 N.m            |
| Local signalling               | without            |
| [Ue] rated operational voltage | 250 V AC 50 Hz     |
| Rated current                  | 10 A               |
| Marking                        | ON-OFF             |
| Marking location               | Marking on surface |
| Height                         | 107 mm             |
| Width                          | 101 mm             |
| Depth                          | 70 mm              |
| Net weight                     | 0.222 kg           |
| Breaking capacity              | 10 kA              |
| Targeted country               | Australia          |
| Rotary handle padlocking       | 2 padlocks 8 mm    |
| Motor M-rating AS3133          | M80 at 250 V       |

### Environment

|                                       |                             |
|---------------------------------------|-----------------------------|
| Ambient air temperature for operation | -25...75 °C                 |
| IP degree of protection               | IP66 conforming to AS 60529 |
| Standards                             | AS/NZS 3133                 |

## Packing Units

|                              |          |
|------------------------------|----------|
| Unit Type of Package 1       | PCE      |
| Number of Units in Package 1 | 1        |
| Package 1 Height             | 10.7 cm  |
| Package 1 Width              | 10.1 cm  |
| Package 1 Length             | 7 cm     |
| Package 1 Weight             | 0.222 kg |

## Offer Sustainability

|                            |  |
|----------------------------|--|
| REACH Regulation           |  <a href="#">REACH Declaration</a>      |
| EU RoHS Directive          | Compliant with Exemptions  |
| China RoHS Regulation      |  <a href="#">China RoHS Declaration</a> |
| RoHS exemption information |  <a href="#">Yes</a>                    |