

Product data sheet

Characteristics

56SW115-GY

56 Series - Switch - 1 Pole - 15A - 250V - grey



Main

Range of product	Series 56
Range	Clipsal - 56 Series
Product brand	Clipsal
Product or component type	Switch
Device presentation	Basic element with full cover plate
Device application	Control
Colour	Cover: grey
Handle colour	Grey
Suitability for isolation	No

Complementary

Switch function	1-pole
Poles description	1P
Control type	Rotary knob
Number of poles	1
Device mounting	Surface
Fixing mode	By screws
Material	PC (polycarbonate)
Tightening torque	0.8 N.m
Local signalling	without
[Ue] rated operational voltage	250 V AC 50 Hz
Rated current	15 A
Breaking capacity	15 kA
Motor M-rating AS3133	M80 at 250 V
Rotary handle padlocking	2 padlocks 8 mm
Marking	ON-OFF
Marking location	Marking on surface
Height	107 mm
Width	101 mm
Depth	83 mm
Net weight	0.38 kg
Targeted country	Australia

Environment

Ambient air temperature for operation	-25...75 °C
IP degree of protection	IP66 conforming to AS 60529
Standards	AS/NZS 3133

Packing Units

Package 1 Weight	0.380 kg
Package 1 Height	92.000 mm
Package 1 width	108.000 mm
Package 1 Length	106.000 mm

Offer Sustainability

EU RoHS Directive	Under investigation
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile