

Product data sheet

Characteristics

56SW220-CG

Clipsal, Surface Switch, 1 Gang, 2 Pole,
500VAC, 20A



Main

| | |
|---------------------|-------------------------------------|
| Range of product | Series 56 |
| Product brand | Clipsal |
| Device presentation | Basic element with full cover plate |

Complementary

| | |
|---|--------------------|
| Switch function | 2-pole |
| [Icm] rated short-circuit making capacity | 1 kA |
| Control type | Rotary knob |
| Number of poles | 2 |
| Device mounting | Surface |
| Fixing mode | By screws |
| Material | PC (polycarbonate) |
| Local signalling | without |
| [Ue] rated operational voltage | 500 V AC |
| Rated current | 20 A |
| Marking | ON-OFF |
| Marking location | Marking on surface |
| [Icw] rated short-time withstand current | 1.2 kA for 1 s |
| [Uimp] rated impulse withstand voltage | 4 kV |

Environment

| | |
|-----------|------------------------------|
| Standards | AS/NZS 3123 AS/NZS 3947-3 |
|-----------|------------------------------|

Packing Units

| | |
|------------------------------|----------|
| Unit Type of Package 1 | PCE |
| Number of Units in Package 1 | 1 |
| Package 1 Height | 11.25 cm |
| Package 1 Width | 11.25 cm |
| Package 1 Length | 10.65 cm |
| Package 1 Weight | 573.0 g |
| Unit Type of Package 2 | CAR |
| Number of Units in Package 2 | 12 |
| Package 2 Height | 25.0 cm |
| Package 2 Width | 21.4 cm |

| | |
|------------------|----------|
| Package 2 Length | 33.8 cm |
| Package 2 Weight | 6.888 kg |

Offer Sustainability

| | |
|----------------------------|---|
| Sustainable offer status | Green Premium product |
| REACH Regulation | REACH Declaration |
| EU RoHS Directive | Compliant EU RoHS Declaration |
| Mercury free | Yes |
| China RoHS Regulation | China RoHS Declaration |
| RoHS exemption information | Yes |
| Environmental Disclosure | Product Environmental Profile |