

Product data sheet

Characteristics

56SWH363-RW

56 Series - Switch - 2 Gang Base Mount - 3 Pole - 63A - 500V - white



Main

Range of product	Series 56
Range	Clipsal - 56 Series
Product brand	Clipsal
Product or component type	Switch
Device presentation	Basic element with full cover plate
Device application	Control
Colour	Cover: white
Handle colour	Red
Suitability for isolation	Yes

Complementary

Switch function	3-pole
Poles description	3P
Control type	Rotary knob
Number of poles	3
Device mounting	Surface
Fixing mode	By screws
Material	PC (polycarbonate)
Tightening torque	0.8 N.m
Local signalling	without
[Ue] rated operational voltage	500 V AC 50 Hz
Rated current	63 A
Breaking capacity	63 kA
Motor M-rating AS3133	M320 at 690 V
Rotary handle padlocking	2 padlocks 8 mm
Marking	Without marking
Height	204 mm
Width	101 mm
Depth	172 mm
Net weight	1.135 kg
Targeted country	Australia

Environment

Ambient air temperature for operation	-25...75 °C
IP degree of protection	IP66 conforming to AS 60529
Standards	AS/NZS 3133

Packing Units

Package 1 Weight	1.135 kg
------------------	----------

Offer Sustainability

EU RoHS Directive	Under investigation
-------------------	---------------------