

Product data sheet

Characteristics

56SWH363A-GY

Clipsal - 56 Series, Surface Switch



Main

Range	Clipsal - 56 Series
Product or component type	Switch
Handle colour	Red
Suitability for isolation	Yes
Colour	Cover: grey

Complementary

Poles description	3P
Control type	Rotary knob
Tightening torque	0.8 N.m
[Ue] rated operational voltage	500 V AC 50 Hz
Rated current	63 A
Breaking capacity	63 kA at 500 V (AC-21A)
Targeted country	Australia
Motor M-rating AS3133	M320 at 690 V
Rotary handle padlocking	2 padlocks 8 mm

Environment

IP degree of protection	IP66 conforming to AS 60529
Standards	AS/NZS 3133

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	1.155 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations