

Product data sheet

Characteristics

56SWH380-RO

56 Series - Switch - 2 Gang Base Mount - 3 Pole - 80A - 500V - orange



Main

Range	Clipsal - 56 Series
Product or component type	Switch
Colour	Cover: orange
Handle colour	Red
Suitability for isolation	Yes

Complementary

Poles description	3P
Control type	Rotary knob
Tightening torque	0.8 N.m
[Ue] rated operational voltage	500 V AC 50 Hz
Rated current	80 A
Breaking capacity	80 kA at 500 V (AC-21A)
Rotary handle padlocking	2 padlocks 8 mm
Targeted country	Australia

Environment

IP degree of protection	IP66 conforming to AS 60529
Standards	AS/NZS 3133

Packing Units

Package 1 Weight	1.233 kg
------------------	----------

Offer Sustainability

EU RoHS Directive	Under investigation
-------------------	---------------------

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.