

Product data sheet

Characteristics

56SWH432-GY

Surface Switch, Clipsal - 56 Series, 2 Gang Four Pole 32A Base Mount



Main

Range	Clipsal - 56 Series
Product or component type	Switch
Handle colour	Red
Suitability for isolation	Yes
Colour	Cover: grey

Complementary

Poles description	4P
Control type	Rotary knob
Tightening torque	0.8 N.m
[Ue] rated operational voltage	500 V AC 50 Hz
Rated current	32 A
Breaking capacity	32 kA at 500 V (AC-21A)
Targeted country	Australia
Motor M-rating AS3133	M168 at 690 V
Rotary handle padlocking	2 padlocks 8 mm

Environment

IP degree of protection	IP66 conforming to AS 60529
Standards	AS/NZS 3133

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	1.095 kg

Offer Sustainability

EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.