

Product data sheet

Characteristics

56SWH432-GY

56 Series - Switch - 2 Gang Base Mount - 4 Pole - 32A - 500V - grey



Main

Range	Clipsal - 56 Series
Product or component type	Switch
Colour	Cover: grey
Handle colour	Red
Suitability for isolation	Yes

Complementary

Poles description	4P
Control type	Rotary knob
Tightening torque	0.8 N.m
[Ue] rated operational voltage	500 V AC 50 Hz
Rated current	32 A
Breaking capacity	32 kA at 500 V (AC-21A)
Targeted country	Australia
Rotary handle padlocking	2 padlocks 8 mm
Motor M-rating AS3133	M168 at 690 V






Environment

IP degree of protection	IP66 conforming to AS 60529
Standards	AS/NZS 3133

Packing Units

Package 1 Weight	1.095 kg
------------------	----------

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant  EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	 Yes
China RoHS Regulation	 China RoHS Declaration
Environmental Disclosure	 Product Environmental Profile