

Product data sheet

Characteristics

56SWHS332-GY

Surface Switch, Clipsal - 56 Series, 2 Gang Three Pole 32A Base Mount

Main

Range	Clipsal - 56 Series
Product or component type	Switch
Handle colour	Grey
Suitability for isolation	Yes
Colour	Cover: grey

Complementary

Poles description	3P
Control type	Rotary knob
Tightening torque	0.8 N.m
[Ue] rated operational voltage	500 V AC 50 Hz
Rated current	32 A
Breaking capacity	32 kA at 500 V (AC-21A)
Targeted country	Australia
Motor M-rating AS3133	M168 at 690 V
Rotary handle padlocking	2 padlocks 8 mm

Environment

IP degree of protection	IP66 conforming to AS 60529
Standards	AS/NZS 3133

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	0.87 kg

Offer Sustainability

EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes