

## Product data sheet

### Characteristics

# 56SWHS332-GY

56 Series - Switch - 2 Gang Base Mount - 3 Pole - 32A - 500V - grey



### Main

Range	Clipsal - 56 Series
Product or component type	Switch
Colour	Cover: grey
Handle colour	Grey
Suitability for isolation	Yes

### Complementary

Poles description	3P
Control type	Rotary knob
Tightening torque	0.8 N.m
[Ue] rated operational voltage	500 V AC 50 Hz
Rated current	32 A
Breaking capacity	32 kA at 500 V (AC-21A)
Motor M-rating AS3133	M168 at 690 V
Rotary handle padlocking	2 padlocks 8 mm
Targeted country	Australia

### Environment

IP degree of protection	IP66 conforming to AS 60529
Standards	AS/NZS 3133

### Packing Units

Package 1 Weight	0.870 kg
------------------	----------

### Offer Sustainability

EU RoHS Directive	Under investigation
-------------------	---------------------

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.