

Product data sheet

Characteristics

56SWHS340-GY

56 Series - Switch - 2 Gang Base Mount - 3 Pole - 40A - 500V - grey



Main

Range	Clipsal - 56 Series
Product or component type	Switch
Colour	Cover: grey
Handle colour	Grey
Suitability for isolation	Yes

Complementary

Poles description	3P
Control type	Rotary knob
Tightening torque	0.8 N.m
[Ue] rated operational voltage	500 V AC 50 Hz
Rated current	40 A
Breaking capacity	40 kA at 500 V (AC-21A)
Targeted country	Australia
Rotary handle padlocking	2 padlocks 8 mm
Motor M-rating AS3133	M220 at 690 V




Environment

IP degree of protection	IP66 conforming to AS 60529
Standards	AS/NZS 3133

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	900.0 g
Package 1 Height	11.2 cm
Package 1 width	10.2 cm
Package 1 Length	20.4 cm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant  EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	 Yes

China RoHS Regulation

 [China RoHS Declaration](#)

Environmental Disclosure

 [Product Environmental Profile](#)
