

Product data sheet

Characteristics

56SWHS340-RO

Clipsal - 56 Series, Surface Switch 2 Gang
Three Pole 40A Base Mount



Main

Range	Clipsal - 56 Series
Product or component type	Switch
Colour	Cover: orange
Handle colour	Grey
Suitability for isolation	Yes

Complementary

Poles description	3P
Control type	Rotary knob
Tightening torque	0.8 N.m
[Ue] rated operational voltage	500 V AC 50 Hz
Rated current	40 A
Breaking capacity	40 kA at 500 V (AC-21A)
Targeted country	Australia
Rotary handle padlocking	2 padlocks 8 mm
Motor M-rating AS3133	M220 at 690 V

Environment

IP degree of protection	IP66 conforming to AS 60529
Standards	AS/NZS 3133

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	11.2 cm
Package 1 Width	10.2 cm
Package 1 Length	20.4 cm
Package 1 Weight	0.9 kg