

## Product data sheet

### Characteristics

# 56SWHS425-RO

56 Series - Switch - 2 Gang Base Mount - 4 Pole - 25A - 500V - orange



### Main

Range	Clipsal - 56 Series
Product or component type	Switch
Colour	Cover: orange
Handle colour	Grey
Suitability for isolation	Yes

### Complementary

Poles description	4P
Control type	Rotary knob
Tightening torque	0.8 N.m
[Ue] rated operational voltage	500 V AC 50 Hz
Rated current	25 A
Breaking capacity	25 kA at 500 V (AC-21A)
Targeted country	Australia
Rotary handle padlocking	2 padlocks 8 mm
Motor M-rating AS3133	M110 at 690 V






### Environment

IP degree of protection	IP66 conforming to AS 60529
Standards	AS/NZS 3133

### Packing Units

Package 1 Weight	0.900 kg
------------------	----------

### Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 <a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant  <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	 <a href="#">Yes</a>
China RoHS Regulation	 <a href="#">China RoHS Declaration</a>
Environmental Disclosure	 <a href="#">Product Environmental Profile</a>