

## Product data sheet

### Characteristics

# 56SWHS440-GY

56 Series - Switch - 2 Gang Base Mount - 4 Pole - 40A - 500V - grey



### Main

Range	Clipsal - 56 Series
Product or component type	Switch
Colour	Cover: grey
Handle colour	Grey
Suitability for isolation	Yes

### Complementary

Poles description	4P
Control type	Rotary knob
Tightening torque	0.8 N.m
[Ue] rated operational voltage	500 V AC 50 Hz
Rated current	40 A
Breaking capacity	40 kA at 500 V (AC-21A)
Targeted country	Australia
Rotary handle padlocking	2 padlocks 8 mm
Motor M-rating AS3133	M220 at 690 V

### Environment

IP degree of protection	IP66 conforming to AS 60529
Standards	AS/NZS 3133

### Packing Units

Unit Type of Package 1	Db
Number of Units in Package 1	1
Package 1 Weight	0.965 kg

### Offer Sustainability

Sustainable offer status	Green Premium product
RECh Regulation	<a href="#">RECh Declaration</a>
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>