

## Product data sheet

### Characteristics

# 56SWHS463LE-CG

## 56 Series - Switch - 2 Gang Base Mount - 4 P - 63A -500V - Less Enclosure



### Main

Range	Clipsal - 56 Series
Product or component type	Switch
Colour	Cover: chemical grey
Handle colour	Grey
Suitability for isolation	Yes

### Complementary

Poles description	4P
Control type	Rotary knob
Tightening torque	0.8 N.m
[Ue] rated operational voltage	500 V AC 50 Hz
Rated current	63 A
Breaking capacity	63 kA at 500 V (AC-21A)
Targeted country	Australia
Rotary handle padlocking	2 padlocks 8 mm
Motor M-rating AS3133	M320 at 690 V

### Environment

IP degree of protection	IP66 conforming to AS 60529
Standards	AS/NZS 3133

### Packing Units

Package 1 Weight	0.530 kg
------------------	----------

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.