

## Product data sheet

### Characteristics

# 56TC-GY

Timer Switch, Clipsal - 56 Series, 240VAC,  
16A, 24h Quartz, Battery Reserve

### Main

Range of product	Series 56
Range	Clipsal - 56 Series
Product brand	Clipsal
Product or component type	Time switch
Assembly Type	Basic element with full cover plate
Device application	Control
Outlet standard deviation	Australian/New Zealand
Colour	Grey (RAL 7035)
Plug, socket category	Low voltage

### Complementary

Poles description	1P + N + E
Installation Type	Surface
Material	Polycarbonate: cover
Local signalling	without
[Ue] rated operational voltage	250 V AC 50 Hz
Rated current	16 A
Protection type	Without protection
Marking	Without marking
Targeted country	Australia
Height	101 mm
Width	101 mm
Depth	102 mm
Net weight	0.6 kg
Contacts material	Pins: phosphor bronze
Plug, socket, control station shape	Straight Angled



### Environment

Ambient air temperature for operation	-25...75 °C
Outlet standard	Industrial
IP degree of protection	IP66 conforming to AS 60529
Standards	AS/NZS 3133 AS/NZS 3123

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	11.6 cm
Package 1 Width	10.8 cm
Package 1 Length	10.9 cm
Package 1 Weight	598.0 g

## Offer Sustainability

EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	 <a href="#">China RoHS Declaration</a>
RoHS exemption information	 <a href="#">Yes</a>