

## Product data sheet

### Characteristics

# 56TC7-GY

## Clipsal - 56 Series, Timer Switch, 240VAC, 16A, 7 Day Quartz, Battery Reserve



### Main

Range of product	Series 56
Range	Clipsal - 56 Series
Product brand	Clipsal
Product or component type	Time switch
Device presentation	Basic element with full cover plate
Device application	Control
Colour	Grey (RAL 7035)
Plug, socket category	Low voltage
Outlet standard	Australian/New Zealand

### Complementary

Poles description	1P + N + E
Device mounting	Surface
Plug, socket, control station shape	Angled Straight
Material	Polycarbonate: cover
Contacts material	Pins: phosphor bronze
Local signalling	without
[Ue] rated operational voltage	250 V AC 50 Hz
Rated current	16 A
Protection type	Without protection
Marking	Without marking
Height	101 mm
Width	101 mm
Depth	102 mm
Net weight	0.6 kg
Targeted country	Australia

### Environment

Ambient air temperature for operation	-25...75 °C
Outlet standard	Industrial
IP degree of protection	IP66 conforming to AS 60529
Standards	AS/NZS 3133 AS/NZS 3123

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	11.3 cm
Package 1 Width	10.5 cm
Package 1 Length	10.6 cm
Package 1 Weight	598.6 g

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>