

## Product data sheet

### Characteristics

# 5754ODPE

## OCCUPANCY, LIGHT LEVEL SENSOR

### SURFACE MOUNT 360 DEGREE



#### Main

Range	C-Bus
Product brand	Clipsal
Product or component type	Occupancy and light level sensor
Device application	Lighting
Product specific application	Staircase monitoring
Sensor type	PIR
Colour	White

#### Complementary

Protection type	Creep zone protection
Type of setting	Light sensitivity adjustable
Number of channels	1
Time delay range	0...1 s (switch-on)
Detection face	Lateral: 4.85 m Frontal: 4.85 m
Movement detection area	9.7 m
Horizontal detection angle	0...360 °
Duty cycle	1080 min
Material	Plastic
Device mounting	Surface
Mounting height	2.7 m

#### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	116 g
Package 1 Height	40 mm
Package 1 width	101 mm
Package 1 Length	101 mm
Unit Type of Package 2	CAR
Number of Units in Package 2	20
Package 2 Weight	2.747 kg
Package 2 Height	16 cm
Package 2 width	28 cm
Package 2 Length	33.5 cm
Unit Type of Package 3	P12
Number of Units in Package 3	960
Package 3 Weight	140.856 kg
Package 3 Height	80 cm
Package 3 width	120 cm
Package 3 Length	110 cm

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	<a href="#">End Of Life Information</a>
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins