

## Product data sheet

### Characteristics

# 60PBBP

Switch 60 Series Mechanism - Push-button -  
Momentary - 250 V - 16 A



#### Main

Range of product	Saturn Series 4000
Product or component type	Push-button
Product brand	Clipsal
Device presentation	Basic element


#### Complementary

Actuator	Push-button
Local signalling	Without light indicator
Fixing mode	By screws
Material	Plastic
Surface finish	Glossy
[Ue] rated operational voltage	250 V AC
Inrush current	16 A
Height	23.5 mm
Depth	40 mm
Embedding depth	31.6 mm
Width	23.5 mm
Mounting position	Vertical

#### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	20.0 g
Package 1 Height	3.3 cm
Package 1 width	2.8 cm
Package 1 Length	6.6 cm

#### Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 <a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant  <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	 Yes
China RoHS Regulation	 <a href="#">China RoHS Declaration</a>
Environmental Disclosure	 <a href="#">Product Environmental Profile</a>