

Product data sheet

Characteristics

60PBBPL

Switch 60 Series Mechanism - Push-button -
Momentary - LED indicator - 250 V - 16 A



Main

Range of product	Saturn Series 4000
Product or component type	Push-button
Product brand	Clipsal
Device presentation	Basic element

Complementary

Actuator	Push-button
Local signalling	Indicator light
Fixing mode	By screws
Material	Plastic
Surface finish	Glossy
[Ue] rated operational voltage	250 V AC
Inrush current	16 A
Height	23.5 mm
Depth	40 mm
Embedding depth	31.6 mm
Width	23.5 mm
Mounting position	Vertical

Packing Units

Package 1 Weight	24.000 g
Package 1 Height	29.000 mm
Package 1 width	25.000 mm
Package 1 Length	60.000 mm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile