

## Product data sheet

### Characteristics

# 60PBBPL/GP

## MOMENTARY PUSH BUTTON SWITCH C/W



### Main

Range of product	Saturn Series 4000
Product or component type	Push-button
Product brand	Clipsal
Device presentation	Basic element




### Complementary

Actuator	Push-button
Local signalling	Indicator light
Fixing mode	By screws
Material	Plastic
Surface finish	Glossy
[Ue] rated operational voltage	250 V AC
Inrush current	16 A
Height	23.5 mm
Depth	40 mm
Embedding depth	31.6 mm
Width	23.5 mm
Mounting position	Vertical

### Packing Units

Package 1 Weight	24.000 g
Package 1 Height	27.000 mm
Package 1 width	30.000 mm
Package 1 Length	58.000 mm

### Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 <a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant  <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	 <a href="#">Yes</a>
China RoHS Regulation	 <a href="#">China RoHS Declaration</a>
Environmental Disclosure	 <a href="#">Product Environmental Profile</a>