

Product data sheet

Characteristics

60PBI

Switch 60 Series Mechanism - Push-button - Intermediate - 250 V - 10 AX



Main

Range of product	Saturn Series
Product or component type	Push-button
Product brand	Clipsal
Device presentation	Basic element

Complementary

Actuator	Push-button
Local signalling	Without light indicator
[Ue] rated operational voltage	250 V AC
Inrush current	10 A
Height	23.5 mm
Depth	40 mm
Embedding depth	31.6 mm
Width	23.5 mm

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	26 g
Package 1 Height	3 cm
Package 1 width	4.6 cm
Package 1 Length	3.1 cm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.