

Product data sheet

Characteristics

60RSM3

Clipsal Saturn 4000, Switch Mechanisms, 4
Position Rotary, 3 On 1 Off



Main

Range of product	Saturn Series 4000
Product brand	Clipsal
Assembly Type	Basic element

Complementary

Control type	Rotary knob
Local signalling	without
[Ue] rated operational voltage	250 V AC
Rated current	10 A
Marking	Without marking

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3 cm
Package 1 Width	4 cm
Package 1 Length	11.3 cm
Package 1 Weight	24 g

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes
Environmental Disclosure	 Product Environmental Profile
Circularity Profile	No need of specific recycling operations