

Product data sheet

Characteristics

610ML12GN

600SeriesIlluminatedModuleWithNeonIndicator, 12VAC DC, WhiteModule, Green



Main

Range of product	600 Series
Product or component type	Illuminated module


Complementary

Material	PC (polycarbonate)
Light source colour	Green
Colour tint	White
Surface finish	Opaque
Installation direction	Vertical
Length	23 mm
Width	23 mm
Depth	25 mm
[Ue] rated operational voltage	12 V
Network type	AC/DC
Network number of phases	1 phase
Number of gangs	1 gang
Mounting mode	Front
Number of terminals	3
Cut-out dimensions	25 mm
Quantity per set	Set of 20
Type of packing	Crate

Packing Units

Package 1 Weight	9.000 g
Package 1 Height	29.000 mm
Package 1 width	30.000 mm
Package 1 Length	30.000 mm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH free of SVHC	Yes
EU RoHS Directive	Compliant  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes

RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information
