

Product data sheet

Characteristics

610MNGNWH

600SeriesIlluminatedModule250VGreen



Main

| | |
|---------------------------|--------------------|
| Range of product | 600 Series |
| Product or component type | Illuminated module |

Complementary

| | |
|--------------------------------|--------------------|
| Material | PC (polycarbonate) |
| Light source colour | Green |
| Colour tint | White |
| Surface finish | Opaque |
| Installation direction | Vertical |
| Length | 23 mm |
| Width | 23 mm |
| Depth | 25 mm |
| [Ue] rated operational voltage | 240/250 V |
| Network type | AC |
| Network number of phases | 1 phase |
| Number of gangs | 1 gang |
| Mounting mode | Front |
| Number of terminals | 2 |
| Cut-out dimensions | 25 mm |
| Quantity per set | Set of 20 |
| Type of packing | Crate |

Packing Units

| | |
|------------------------------|---------|
| Unit Type of Package 1 | PCE |
| Number of Units in Package 1 | 1 |
| Package 1 Weight | 0.001 g |

Offer Sustainability

| | |
|--------------------------|---|
| Sustainable offer status | Green Premium product |
| RECh Regulation |  RECh Declaration |
| RECh free of SVHC | Yes |
| EU RoHS Directive | Compliant  EU RoHS Declaration |
| Toxic heavy metal free | Yes |
| Mercury free | Yes |
| China RoHS Regulation |  China RoHS Declaration |

| | |
|----------------------------|---|
| RoHS exemption information | Yes |
| Environmental Disclosure | Product Environmental Profile |
| Circularity Profile | End Of Life Information |
