

## Product data sheet

### Characteristics

# 6220-0N

Exhaust fan, Airflow, ceiling, 250mm blade dia, white



### Main

Range of product	Airflow
Range	Airflow
Product brand	Clipsal
Product or component type	Exhaust fan
Product destination	Ceiling fitting
Main colour tint	White
Colour tint	White

### Complementary

Provided equipment	Fan 120 mm 250 mm
[Ue] rated operational voltage	230 V AC 50 Hz
Material	ABS (acrylonitrile butadiene-styrene)
Air flow	750 m <sup>3</sup> /h
Diameter	320 mm impeller:
Power consumption in W	30 W
[In] rated current	0.17 A full load
Plug & lead length	560 mm
Cut-out dimensions	290 mm diameter
Depth	120 mm
Motor type	Sleeve bearing
Number of blades	6
Noise level	52 dB
Fan type	Axial

### Environment

IP degree of protection	IPx4
-------------------------	------

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	32.5 cm
Package 1 Width	13 cm
Package 1 Length	32.5 cm
Package 1 Weight	2.395 kg
Unit Type of Package 2	PAL
Number of Units in Package 2	48
Package 2 Height	86 cm
Package 2 Width	113 cm

Package 2 Length	113 cm
Package 2 Weight	141 kg

### Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations
Halogen content performance	Halogen free plastic parts product

### Contractual warranty

Warranty	3 Years
----------	---------