

Product data sheet

Characteristics

6230-0

Airflow Ceiling Mounted Exhaust Fans 300mm



Main

Product brand	Clipsal
---------------	---------

Complementary

[Ue] rated operational voltage	240 V AC
Air flow	660 m3/h
Diameter	300 mm impeller:
Power consumption in W	54 W
[In] rated current	0.34 A full load

Packing Units

Unit Type of Package 1	Db
Number of Units in Package 1	1
Package 1 Height	17.5 cm
Package 1 Width	38.5 cm
Package 1 Length	39 cm
Package 1 Weight	2809 g

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information