

Product data sheet

Characteristics

6230-0

Airflow, Ceiling Mounted Exhaust Fans 300mm



Main

Range of product	Airflow
Product brand	Clipsal

Complementary

[Ue] rated operational voltage	240 V AC
Air flow	660 m3/h
Diameter	300 mm impeller:
Power consumption in W	54 W
[In] rated current	0.34 A full load

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	17.5 cm
Package 1 Width	38.5 cm
Package 1 Length	39 cm
Package 1 Weight	2809 g

Offer Sustainability

EU RoHS Directive	Compliant with Exemptions
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations Circularity Profile

The information provided in this documentation contains general descriptions and/or technical characteristics of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.