

Product data sheet

Characteristics

666TMB24-WH

24V PIEZO BUZZER 30MA

Main

Colour	White
Product brand	Clipsal
Range of product	Series 600
Noise level	90 dB
Colour	Housing: white

Complementary

Colour code	WH
[Ue] rated operational voltage	24 V DC
Supply circuit type	DC
Current consumption	0.02 A

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.