

## Product data sheet

### Characteristics

# 66CV463-RG

## SWITCHED SOCKET PVC IP66 4 PIN 63A



### Main

Range of product	Series 66CV
Product brand	Clipsal
Device application	Power supply
Colour	Resistant grey

### Complementary

Number of poles	4
Number of modules	3
Number of power socket outlets	1 protective cover
[In] rated current	63 A
[Ue] rated operational voltage	500 V AC
Material	Plastic: housing
Depth	215 mm
Width	160 mm
Height	320 mm

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	4.07 kg
Package 1 Height	21.5 cm
Package 1 width	16 cm
Package 1 Length	32 cm

### Offer Sustainability

EU RoHS Directive	Under investigation
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>