

## Product data sheet

### Characteristics

# 66CV563-RG

## Switched Socket Outlet, 66 Series, 500V, 63A, 5 Round PIN, IP66

### Main

Range of product	Series 66CV
Product brand	Clipsal
Device application	Power supply
Colour	Resistant grey

### Complementary

Number of poles	5
Number of modules	4
Number of power socket outlets	1 protective cover
[In] rated current	63 A
[Ue] rated operational voltage	500 V AC
Material	Plastic: housing
Depth	215 mm
Width	160 mm
Height	320 mm

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	16.4 cm
Package 1 Width	21.8 cm
Package 1 Length	33.6 cm
Package 1 Weight	4.032 kg

### Offer Sustainability

REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant with Exemptions
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.