

Product data sheet

Characteristics

66CV763-RG

SWITCHED SOCKET PVC IP66 7 PIN 63A



Main

Range of product	Series 66CV
Product brand	Clipsal
Device application	Power supply
Colour	Resistant grey

Complementary

Number of poles	7
Number of modules	4
Number of power socket outlets	1 protective cover
[In] rated current	63 A
[Ue] rated operational voltage	500 V AC
Material	Plastic: housing
Depth	215 mm
Width	160 mm
Height	320 mm

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	4.5 kg
Package 1 Height	215 mm
Package 1 width	160 mm
Package 1 Length	320 mm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile