

Product data sheet

Characteristics

66P750-RO

Heavy Duty Straight Plug, 66 Series, IP66, 500V 50A - 7 Round Pins



Main

Range of product	Series 66P
Product brand	Clipsal

Complementary

[In] rated current	50 A
[Ue] rated operational voltage	500 V 50/60 Hz conforming to EN 60309-2
Colour	Resistant orange
Material	Plastic
Connections - terminals	Screw terminal
Cable entry	Cable gland
Plug, socket, control station shape	Straight
Duration	7 h

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	1.000 kg

Offer Sustainability

REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant with Exemptions
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Circularity Profile	No need of specific recycling operations

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.