

Product data sheet

Characteristics

67P432/3

Plug Top, 67 Series, Straight, 4 PIN, 32A, IP67, 3h



Main

Range of product	Series 67
Product brand	Clipsal




Complementary

[In] rated current	32 A
[Ue] rated operational voltage	400 V 50/60 Hz conforming to EN 60309-2
Cable entry	Cable gland
Plug, socket, control station shape	Straight
Duration	6 h

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	100 cm
Package 1 Width	100 cm
Package 1 Length	175 cm
Package 1 Weight	0.4 kg
Unit Type of Package 2	CAR
Number of Units in Package 2	10
Package 2 Height	210 cm
Package 2 Width	210 cm
Package 2 Length	480 cm
Package 2 Weight	4 kg

Offer Sustainability

Sustainable offer status	Green Premium product
EU RoHS Directive	Compliant with Exemptions
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes
Environmental Disclosure	 Product Environmental Profile
Circularity Profile	No need of specific recycling operations