

## Product data sheet

### Characteristics

# 67SO316/6

## Socket Outlets, 67 Series, IP67, 220/240V, 16A, 6 Hour, 3 Round Pins

### Main

Range of product	Series 67
Product brand	Clipsal



### Complementary

[In] rated current	16 A
[Ue] rated operational voltage	230 V 50/60 Hz conforming to EN 60309-2
Voltage colour	Blue
Duration	6 h
Socket number	1

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	11.0 cm
Package 1 Width	9.2 cm
Package 1 Length	14.2 cm
Package 1 Weight	0.3 kg
Unit Type of Package 2	CAR
Number of Units in Package 2	10
Package 2 Height	24.5 cm
Package 2 Width	25.3 cm
Package 2 Length	29.8 cm
Package 2 Weight	3.0 kg

### Offer Sustainability

EU RoHS Directive	Compliant with Exemptions
China RoHS Regulation	 <a href="#">China RoHS Declaration</a>
RoHS exemption information	 <a href="#">Yes</a>

The information provided in this documentation contains general descriptions and/or technical characteristics of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.