

## Product data sheet

### Characteristics

# 7006A

## Airflow, Performance Exhaust Fan, Wall Mount, 150mm, Axial



### Main

Range of product	MaxAir Airflow
Product brand	Clipsal

### Complementary

[Ue] rated operational voltage	230...240 V AC
Air flow	360 m3/h
Diameter	148 mm impeller:
Power consumption in W	45 W
[In] rated current	0.27 A full load

### Environment

IP degree of protection	IPx4
-------------------------	------

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	21.0 cm
Package 1 Width	25.0 cm
Package 1 Length	25.0 cm
Package 1 Weight	1945.0 g

### Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations <a href="#">Circularity Profile</a>