

Product data sheet

Characteristics

7006A

FAN EXH WALL 150MM-AUTO LOUVRE



Main

Product brand	Clipsal
---------------	---------

Complementary

[Ue] rated operational voltage	230...240 V AC
Air flow	360 m3/h
Diameter	148 mm impeller:
Power consumption in W	45 W
[In] rated current	0.27 A full load

Environment

IP degree of protection	IPx4
-------------------------	------

Packing Units

Package 1 Weight	1945.000 g
Package 1 Height	210.000 mm
Package 1 width	250.000 mm
Package 1 Length	250.000 mm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile