

Product data sheet

Characteristics

7006AN

Exhaust fan, Airflow, wall, 150mm blade dia, auto louvre, white



Main

Range of product	Airflow
Range	Airflow
Product brand	Clipsal
Product or component type	Exhaust fan
Product destination	For wall
Main colour tint	White
Colour tint	White

Complementary

Provided equipment	Fan 245 mm 245 mm 150 mm
[Ue] rated operational voltage	230 V AC 50 Hz
Material	ABS (acrylonitrile butadiene-styrene)
Air flow	360 m ³ /h
Diameter	148 mm impeller:
Power consumption in W	45 W
[In] rated current	0.27 A full load
Cut-out dimensions	180 mm diameter
Depth	110 mm
Motor type	Sleeve bearing
Number of blades	7
Noise level	49 dB
Fan type	Axial

Environment

IP degree of protection	IPx4
-------------------------	------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	20.5 cm
Package 1 Width	24.5 cm
Package 1 Length	24.5 cm
Package 1 Weight	1.942 kg
Unit Type of Package 2	PAL
Number of Units in Package 2	64
Package 2 Height	103 cm
Package 2 Width	113 cm
Package 2 Length	113 cm
Package 2 Weight	150 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations

Contractual warranty

Warranty	3 Years
----------	---------