

## Product data sheet

### Characteristics

# 7007AN

Exhaust fan, Airflow, window, 150mm blade dia, pull cord louvre, white



#### Main

Range of product	Airflow
Range	Airflow
Product brand	Clipsal
Product or component type	Exhaust fan
Product destination	Window
Main colour tint	White
Colour tint	White

#### Complementary

Provided equipment	Fan 245 mm 245 mm 150 mm
[Ue] rated operational voltage	230 V AC 50 Hz
Material	ABS (acrylonitrile butadiene-styrene)
Air flow	360 m <sup>3</sup> /h
Diameter	148 mm impeller:
Power consumption in W	45 W
[In] rated current	0.27 A full load
Cut-out dimensions	213 mm diameter
Motor type	Sleeve bearing
Number of blades	7
Noise level	50 dB
Fan type	Axial

#### Environment

IP degree of protection	IPx4
-------------------------	------

#### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	20.5 cm
Package 1 Width	24.5 cm
Package 1 Length	24.5 cm
Package 1 Weight	2.292 kg
Unit Type of Package 2	PAL
Number of Units in Package 2	64
Package 2 Height	103 cm
Package 2 Width	113 cm
Package 2 Length	113 cm
Package 2 Weight	173 kg

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations
Halogen content performance	Halogen free plastic parts product

## Contractual warranty

Warranty	3 Years
----------	---------