

Product data sheet

Characteristics

7105A

FAN EXH WIND 200MM-AUTO LOUVRE



Main

Product brand	Clipsal
---------------	---------

Complementary

[Ue] rated operational voltage	230...240 V AC
Air flow	600 m3/h
Diameter	188 mm impeller:
Power consumption in W	38 W
[In] rated current	0.18 A full load




Environment

IP degree of protection	IPx4
-------------------------	------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	3.24 kg
Package 1 Height	22.2 cm
Package 1 width	46.2 cm
Package 1 Length	28.4 cm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	 Yes
China RoHS Regulation	 China RoHS Declaration
Environmental Disclosure	 Product Environmental Profile