

## Product data sheet

### Characteristics

# 7105A

Airflow, Performance Exhaust Fan, Window Mount, 190mm, Axial



### Main

Range of product	Airflow MaxAir
Product brand	Clipsal

### Complementary

[Ue] rated operational voltage	230...240 V AC
Air flow	600 m3/h
Diameter	188 mm impeller:
Power consumption in W	38 W
[In] rated current	0.18 A full load

### Environment

IP degree of protection	IPx4
-------------------------	------

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	22.2 cm
Package 1 Width	46.2 cm
Package 1 Length	28.4 cm
Package 1 Weight	3.24 kg

### Offer Sustainability

REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant with Exemptions
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations <a href="#">Circularity Profile</a>