

Product data sheet

Characteristics

7108A

FAN EXH WALL 200MM-P/CORD LOUV



Main

Product brand	Clipsal
---------------	---------

Complementary

[Ue] rated operational voltage	230...240 V AC
Air flow	600 m3/h
Diameter	188 mm impeller:
Power consumption in W	38 W
[In] rated current	0.18 A full load

Environment

IP degree of protection	IPx4
-------------------------	------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	2808 g
Package 1 Height	27.2 cm
Package 1 width	21.2 cm
Package 1 Length	27.4 cm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile