

## Product data sheet

### Characteristics

# 727-WE

## Standard Series, Universal Shaver Socket Outlet, 240/110VAC



### Main

Range of product	Standard Series
Product or component type	Switched socket
Product brand	Clipsal

### Complementary

Control type	ON/OFF button
Number of gangs	1 gang
Pin number	3
Number Of Outlets	1
Mounting Type	By screws
Local signalling	Without light indicator
[Ue] rated operational voltage	110/240 V AC
Depth	17 mm
Length	258 mm
Width	73 mm
Mounting Centers	230 x 40 mm

### Environment

Standards	AS/NZS 3100 AS/NZS 3112 AS/NZS 3133:approval number S/1
-----------	---

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	1.7 cm
Package 1 Width	7.3 cm
Package 1 Length	25.8 cm
Package 1 Weight	0.9 kg

### Offer Sustainability

RECh Regulation	<a href="#">RECh Declaration</a>
EU RoHS Directive	Compliant with Exemptions
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations