

Product data sheet

Characteristics

727V-WE

SOCKET OUTLET VERT SHAVER



Main

| | |
|---------------------------|-----------------|
| Range of product | Standard Series |
| Product or component type | Switched socket |
| Product brand | Clipsal |

Complementary

| | |
|--------------------------------|-------------------------|
| Control type | ON/OFF button |
| Number of gangs | 1 gang |
| Pin number | 3 |
| Number of power socket outlets | 1 |
| Fixing mode | By screws |
| Local signalling | Without light indicator |
| Mounting position | Vertical |
| [Ue] rated operational voltage | 110/240 V AC |
| Depth | 18 mm |
| Length | 184 mm |
| Width | 85 mm |
| Fixing center | 152 mm |

Environment

| | |
|-----------|---|
| Standards | AS/NZS 3100 AS/NZS 3112 AS/NZS 3133:approval number S/1 |
|-----------|---|

Packing Units

| | |
|------------------------------|---------|
| Unit Type of Package 1 | Db |
| Number of Units in Package 1 | 1 |
| Package 1 Height | 1.8 cm |
| Package 1 Width | 8.5 cm |
| Package 1 Length | 18.4 cm |
| Package 1 Weight | 0.8 kg |

Offer Sustainability

| | |
|----------------------------|---|
| Sustainable offer status | Green Premium product |
| REACH Regulation | REACH Declaration |
| EU RoHS Directive | Compliant EU RoHS Declaration |
| Mercury free | Yes |
| China RoHS Regulation | China RoHS Declaration |
| RoHS exemption information | Yes |
| Environmental Disclosure | Product Environmental Profile |