

Product data sheet

Characteristics

750WP-GY

Motion Sensor Infrascan - Passive infrared -
Outdoor - 18m detection range - 2-Wire - 240 V
- 5 A - Grey



Main

Range	Infrascan
Product brand	Clipsal
Product or component type	Movement sensor
Colour	Grey

Complementary

[Ue] rated operational voltage	200...265 V AC
Network frequency	50 Hz
Power range	<= 40 W
Mounting support	Wall Ceiling
Mounting height	2.4 m
Colour code	GY





Environment

IP degree of protection	IP66
Ambient air temperature for operation	0...50 °C

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	8.5 cm
Package 1 Width	13.0 cm
Package 1 Length	16.5 cm
Package 1 Weight	0.38 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant  EU RoHS Declaration
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes

Environmental Disclosure	 Product Environmental Profile
Circularity Profile	 End Of Life Information