

## Product data sheet

### Characteristics

# 750WPR-GY

Motion Sensor Infrascan - Passive infrared -  
Outdoor - 18m detection range - 3-wire - 240 V  
- 10 A - Grey



#### Main

Range	Infrascan
Product brand	Clipsal
Product or component type	Movement sensor
Colour	Grey

#### Complementary

[Ue] rated operational voltage	200...265 V AC
Network frequency	50 Hz
Mounting support	Wall Ceiling
Mounting height	2.4 m
Colour code	GY





#### Environment

IP degree of protection	IP66
Ambient air temperature for operation	0...50 °C

#### Packing Units

Unit Type of Package 1	Db
Number of Units in Package 1	1
Package 1 Height	16.5 cm
Package 1 Width	12.6 cm
Package 1 Length	8.3 cm
Package 1 Weight	331.0 g

#### Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 <a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant  <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	 <a href="#">China RoHS Declaration</a>
RoHS exemption information	 <a href="#">Yes</a>

---

Environmental Disclosure

 [Product Environmental Profile](#)

---

Circularity Profile

 [End Of Life Information](#)

---