

Product data sheet

Characteristics

750WPR5-BK

Movement sensor, Infrascan, Passive infrared, Outdoor, 18m detection range, 3 wire, 240V 10A, black



Main

Range	Infrascan
Product brand	Clipsal
Product or component type	Movement sensor
Sensor type	PIR
Colour	Black

Complementary

[Ue] rated operational voltage	200...265 V AC
Network frequency	50 Hz
[In] rated current	10 A
Movement detection area	18 m
Device mounting	Surface
Mounting support	Wall Ceiling
Mounting height	2.4 m
Colour code	BK

Environment

IP degree of protection	IP66
Ambient air temperature for operation	0...50 °C

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	316.0 g
Package 1 Height	16.2 cm
Package 1 width	8 cm
Package 1 Length	12 cm
Unit Type of Package 2	S03
Number of Units in Package 2	5
Package 2 Weight	1.7 kg
Package 2 Height	30 cm
Package 2 width	30 cm
Package 2 Length	40 cm
Unit Type of Package 3	P12
Number of Units in Package 3	540
Package 3 Weight	198.0 kg

Package 3 Height	150 cm
Package 3 width	80 cm
Package 3 Length	120 cm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information