

Product data sheet

Characteristics

750WPR5-BK

Clipsal Infrascan, Outdoor Infrascan, PIR motion sensor, 3 wire, IP66



Main

Range	Infrascan
Product brand	Clipsal
Product or component type	Movement sensor
Sensor type	PIR
Colour	Black

Complementary

[Ue] rated operational voltage	200...265 V AC
Network frequency	50 Hz
[In] rated current	10 A
Movement detection area	18 m
Device mounting	Surface
Mounting support	Wall Ceiling
Mounting height	2.4 m
Colour code	BK

Environment

IP degree of protection	IP66
Ambient air temperature for operation	0...50 °C

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	16.2 cm
Package 1 Width	8.0 cm
Package 1 Length	12.0 cm
Package 1 Weight	316.0 g
Unit Type of Package 2	S03
Number of Units in Package 2	5
Package 2 Height	30.0 cm
Package 2 Width	30.0 cm
Package 2 Length	40.0 cm
Package 2 Weight	1.7 kg
Unit Type of Package 3	P12
Number of Units in Package 3	540
Package 3 Height	150.0 cm

Package 3 Width	80.0 cm
Package 3 Length	120.0 cm
Package 3 Weight	198.0 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information