

Product data sheet

Characteristics

752DALIRC

PIR sensor, Master, 360deg, DALI output,
Remote control option



Main

Range of product	ARGUS standard movement detector
Range	ARGUS
Product or component type	Presence detector with IR receiver
Load type	Ballast: 25 with Dali electronic ballast
Colour tint	White

Complementary

Network frequency	50/60 Hz
Input function	Switch
Communication port protocol	DALI
Number of channels	2
Type of setting	Pre-programmed time
Control type	Movement sensor
Function available	Override switches Master function Switching, toggling, dimming Constant light control
Light intensity adjustment	10...2000 lux
Horizontal detection angle	360 °
Detection range	Radius: 4000 mm
Device mounting	Surface Flush
Mounting height	2.5 m

Environment

IP degree of protection	IP20
-------------------------	------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	12.5 cm
Package 1 Width	10.5 cm
Package 1 Length	12.5 cm
Package 1 Weight	300.4 g

Offer Sustainability

REACH Regulation	REACH Declaration
EU RoHS Directive	Not compliant
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins